



## Snipe nose pliers, angled, chrome-plated, with grips, overall length: 200mm



### Order data

Order number	713501 200
GTIN	
Item class	73F

### Description

#### Version:

Very long snipe nose jaws. Cutting edges induction hardened (approx. 61 HRC), suitable for cutting hard and soft wire. Serrated inside jaws.

Pliers, chrome-plated, handles with ergonomically optimised multi-component covers and KNIPEXtend interface.

KNIPEXtend is used to connect extensions, such as ColourCode Clips (CCCs) for customisation or TetheredTool Clips (TTCs) for attaching a Tethered Tools fall protection device.

#### Standard:

**DIN ISO 5745**

#### Material:

Chrome vanadium steel, drop-forged and oil-hardened.

#### Note:

Previous model No. 713500 can still be ordered until the KNIPEXtend models are available.

### Technical description

overall length	200 mm
Jaw length	73 mm
Jaw design	snipe nose, angled (40° – 45°)
Standard	DIN ISO 5745
Jaw characteristics	Cutting edges induction hardened (approx. 60 HRC)
Type of jaws	inside serrated

Handle	Multi-component covering
Material	Chrome vanadium steel, drop-forged and oil-hardened
Surface	chrome-plated
Type of product	Multi-function pliers