



Snipe nose pliers, chrome-plated, with grips, overall length: 160mm



Order data

Order number	712201 160
GTIN	
Item class	73F

Description

Version:

With long, slim jaws tapering snipe-nosed. Flush fitting joint with no play. Serrated inside jaws. Pliers chrome-plated, handles with multi-component covers and KNIPEXtend interface. KNIPEXtend is used to connect extensions, such as ColourCode Clips (CCCs) for customisation or TetheredTool Clips (TTCs) for attaching a Tethered Tools fall protection device.

Standard:

DIN ISO 5745

Material:

Chrome vanadium electro-steel, drop-forged and oil-hardened.

Note:

Previous model No. 712200 can still be ordered until the KNIPEXtend models are available.

Technical description

Type of jaws	inside serrated
Standard	DIN ISO 5745
non-sparking	no
with cutting edge	no
Material	Chrome vanadium electrosteel
Material	drop forged
Material	oil-hardened
Jaw length	54 mm

Jaw design	snipe nose
Jaw design	straight
Handle	plastic coated
Surface	chrome-plated
overall length	160 mm
Type of product	Snipe nose pliers