



Side cutter chrome-plated, with grips, overall length: 180mm



Order data

Order number	724861 180
GTIN	4003773043706
Item class	73F

Description

Version:

Slim shape with induction hardened cutting edges (approx. 62 HRC).

Pliers chrome-plated, handles with multi-component covers and KNIPEXtend interface.

KNIPEXtend is used to connect extensions, such as ColourCode Clips (CCCs) for customisation or TetheredTool Clips (TTCs) for attaching a Tethered Tools fall protection device.

Standard:

DIN ISO 5749

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Note:

Previous model No. 724860 can still be ordered until the KNIPEXtend models are available.

Technical description

Cutting capacity hard wire up to Ø	2.5 mm
overall length	180 mm
Cutting capacity soft wire up to Ø	4 mm
Standard	DIN ISO 5749
Handle	Multi-component covering
Manufacturing process	Cutting edges induction hardened (approx. 62 HRC)
Surface	chrome-plated

Heavy-duty diagonal side cutter	no
with selectable return spring	no
Type of product	Cutting pliers