

Garant**All-steel clamp, Jaw capacity: 300mm****Order data**

Order number	860482 300
GTIN	4067263742906
Item class	81D

Description**Version:**

Beam / fixed jaw made of bright drawn steel, moving jaw of forged steel, each hardened and electro galvanised. Smooth running steel spindle with trapezoidal thread, burnished. Moving jaw with integral **spindle locking prevents the release** of the spindle even in case of vibrations. Maximum force transfer due to **power grip** with easy-grip Haptoprene surface and impact-resistant PP core. Surface structure is anti-slip even with wet, oily hands.

Technical description

Throat	140 mm
Cross section of the slide rail	25×12 mm
Jaw capacity	300 mm
Type of product	Clamp

