

**Garant****All-steel clamp with fold-out handle, Jaw capacity: 400mm****Order data**

Order number	860492 400
GTIN	4067263743026
Item class	81D

**Description****Version:**

Beam / fixed jaw made of bright drawn steel, moving jaw of forged steel, each hardened and electro galvanised. Smooth running steel spindle with trapezoidal thread, burnished. Moving jaw with integral **spindle locking prevents the release** of the spindle even in case of vibrations. Maximum force transfer due to **power grip** with easy-grip Haptoprene surface and impact-resistant PP core. Surface structure is anti-slip even with wet, oily hands. All-steel clamp with fold-out handle. Quick approach and clamping of the workpiece with the handle engaged in the vertical position. **Powerful and convenient working with the handle folded out.**

**Technical description**

Cross section of the slide rail	25×12 mm
Throat	120 mm
Jaw capacity	400 mm
Type of product	Clamp

