

metabo
Cordless straight die grinder without rechargeable battery, Type: GVB18LTXBL

Order data

Order number	077272 GVB18LTXBL
GTIN	4061792247307
Item class	03D

Description
Version:

The straight die grinders from Metabo® are among the slimmest and most compact machines on the market. The powerful motors of the mains-operated and cordless straight die grinders offer maximum productivity with high precision in all applications.

Cordless straight die grinder with high (and variable) speed for heavy-duty grinding applications even in tight places.

- **Restart protection: Prevents unintentional startup after battery change.**
- **Spindle lock for easy tool change.**

Advantage:

Batteries are 100% compatible – now also across different manufacturers.

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for "Cordless Alliance System".

Supplied with:

Without battery and charger, including collet 6 mm, rubber cap, dust filter, open-ended spanner.

Note:

See No. 073870 – 073890 for suitable batteries and chargers.

Technical description

Number of rechargeable batteries contained	0
--	---

maximum collet Ø	6 mm
suitable battery - supplier / battery type / voltage	Type CAS 18 V
Speed range	8000 - 28000 min ⁻¹
electronic speed pre-selection	yes
Battery voltage	18 V
Weight	1.4 kg
Manufacturer's designation	GVB18LTXBL11-28
Power supply	Mains operated
Type of product	Straight die grinder