

**Marking out, drilling, deburring, Number of tools: 4****Order data**

|              |               |
|--------------|---------------|
| Order number | 954857 4      |
| GTIN         | 2050002075450 |
| Item class   | 91A           |

**Description****Version:**

Popular tool sets in two-colour PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. **Upper layer is anthracite**, the underlying **contrast colour is grey**, thereby indicating any missing tools.

**Supplied with:**

Rigid foam inlay, empty No. 952001 size 954857: 1 pc.

GARANT jobber drill set HSS No. 115120 size 1-13KB: 1 pc.

GARANT hand deburrer 90° No. 150400 size 16.5: 1 pc.

HOLEX carbide scriber No. 458800 size HM: 1 pc.

Centre punch special quality No. 748900 size 120/10: 1 pc.

**Technical description**

|                 |        |
|-----------------|--------|
| Width           | 200 mm |
| Depth in G      | 10     |
| Width in G      | 8      |
| Depth           | 250 mm |
| Number of tools | 4      |

|                                       |                  |
|---------------------------------------|------------------|
| Version                               | with tool kit    |
| Rigid foam quality LD45, thickness    | 30 mm            |
| Degree of fill of a drawer in units   | 8×10             |
| Smallest suitable drawer front height | 100 mm           |
| Type of product                       | Rigid foam inlay |

## Accessories

|   |               |
|---|---------------|
| Rigid foam inlay for tool sets suitable for rigid foam set 954857     | 952001 954857 |
| Jobber drill set HSS No. 114150 in a case Type 1-13KB                 | 115120 1-13KB |
| Hand deburrer 90° External Ø 16,5 mm                                  | 150400 16,5   |
| Straight carbide scriber Type HM                                      | 458800 HM     |
| Centre punch, special quality, chrome-plated overall length 120/10 mm | 748900 120/10 |