

HOLEX**Wheel brush Steel wire 0.50 mm, Brush \varnothing D1 \times bore \varnothing d1 / thread M:
178X22mm****Order data**

Order number	571203 178X22
GTIN	4067263906599
Item class	57H

Description**Version:**

Straight round brush with smooth wire 0.50 mm, **knotted** and firmly crimped into the steel body. **Very aggressive brushing effect with high wear resistance.**

Application:

For heavy brush work, e.g. descaling, removing rust, removing paint, roughening, cleaning metal parts, also for cleaning formwork boards.

Left knotted, reliably avoids premature unwinding.

Technical description

maximum speed	12500 min ⁻¹
Number of twisted knots	38
Bore \varnothing d ₁	22 mm
Brush \varnothing D ₁	178 mm
Length of brush section H ₁	38 mm

Bristle thickness	0.5 mm
Bristle width L ₁	14 mm
Brush material	Steel wire
Type of product	Wheel brush