


HOLEX

Wheel brush Right-left knotted, steel wire 0.50 mm, Brush \varnothing D1 \times bore \varnothing d1 / thread M: 115X22mm



Order data

Order number	571207 115X22
GTIN	4067263906704
Item class	57H

Description

Version:

Straight round brush with smooth wire 0.50 mm, **knotted** and firmly crimped into the steel body. **Very aggressive brushing effect with high wear resistance.**

Application:

For heavy brush work, e.g. descaling, removing rust, removing paint, roughening, cleaning metal parts, also for cleaning formwork boards.

Right-left knotted for increased aggressiveness for heavy-duty brushing work. Very suitable for use at corners and edges, with a smooth action.

Technical description

maximum speed	12500 min ⁻¹
Bristle width L ₁	14 mm
Brush \varnothing D ₁	115 mm
Bore \varnothing d ₁	22 mm

Number of twisted knots	20
Bristle thickness	0.5 mm
Length of brush section H ₁	24 mm
Brush material	Steel wire
Type of product	Wheel brush