

HOLEX**Wheel brush Stainless steel wire 0.50 mm, Brush $\varnothing D_1 \times$ bore $\varnothing d_1$ / thread M: 115X22mm****Order data**

Order number	571253 115X22
GTIN	4067263906728
Item class	57H

Description**Version:**

Straight round brush with smooth wire 0.50 mm, **knotted** and firmly crimped into the steel body. **Very aggressive brushing effect with high wear resistance.**

Application:

For heavy brush work, e.g. descaling, removing rust, removing paint, roughening, cleaning metal parts, also for cleaning formwork boards.

Technical description

Number of twisted knots	20
maximum speed	12500 min ⁻¹
Length of brush section H ₁	24 mm
Bore $\varnothing d_1$	22 mm
Brush $\varnothing D_1$	115 mm
Bristle width L ₁	14 mm

Bristle thickness	0.5 mm
Brush material	Stainless steel wire
Type of product	Wheel brush