

**HOLEX****Dished bevel brush Steel wire 0.50 mm, Brush Ø D1× thread M: 125XM14mm****Order data**

Order number	571303 125XM14
GTIN	4067263906742
Item class	57H

**Description****Version:**

Cranked **conical brush** with smooth wire 0.50 mm, **knotted** and firmly crimped into the steel body. **Very aggressive brushing effect with high wear resistance.**

**Application:**

**Left knotted**, reliably avoids premature unwinding.

Ideal for working where access is difficult and for heavy brush work, e.g. descaling, removing rust, removing paint, roughening, cleaning metal parts, also for cleaning formwork boards.

With **internal thread M14**, for direct mounting **on angle grinders**.

**Technical description**

Thread M	M14
Bristle width L <sub>1</sub>	12 mm
maximum speed	12500 min <sup>-1</sup>
Brush material	Steel wire
Twisted knotting	left knotted

Type of product

Bevel brush