

HOLEX**Dished bevel brush Stainless steel wire 0.50 mm, Brush Ø D1× thread M:
115XM14mm****Order data**

| | |
|--------------|----------------|
| Order number | 571353 115XM14 |
| GTIN | 4067263906766 |
| Item class | 57H |

Description**Version:**

Cranked **conical brush** with smooth wire 0.50 mm, **knotted** and firmly crimped into the steel body. **Very aggressive brushing effect with high wear resistance.**

Application:

Left knotted, reliably avoids premature unwinding.

Ideal for working where access is difficult and for heavy brush work, e.g. descaling, removing rust, removing paint, roughening, cleaning metal parts, also for cleaning formwork boards.

With **internal thread M14**, for direct mounting **on angle grinders.**

Technical description

| | |
|------------------------------|--------|
| Bristle width L ₁ | 12 mm |
| Bristle thickness | 0.5 mm |
| Brush Ø D ₁ | 115 mm |
| Thread M | M14 |

| | |
|--|-------------------------|
| Length of brush section H ₁ | 24 mm |
| Number of twisted knots | 20 |
| maximum speed | 12500 min ⁻¹ |
| Brush material | Stainless steel wire |
| Twisted knotting | left knotted |
| Type of product | Bevel brush |