

**Dished bevel brush Stainless steel wire 0.50 mm, Brush Ø D1× thread M: 125XM14mm****Order data**

Order number	571353 125XM14
GTIN	4067263906773
Item class	57H

Description**Version:**

Cranked **conical brush** with smooth wire 0.50 mm, **knotted** and firmly crimped into the steel body. **Very aggressive brushing effect with high wear resistance.**

Application:

Left knotted, reliably avoids premature unwinding.

Ideal for working where access is difficult and for heavy brush work, e.g. descaling, removing rust, removing paint, roughening, cleaning metal parts, also for cleaning formwork boards.

With **internal thread M14**, for direct mounting **on angle grinders**.

Technical description

Bristle thickness	0.5 mm
Number of twisted knots	20
maximum speed	12500 min ⁻¹
Brush Ø D ₁	125 mm

Length of brush section H ₁	29 mm
Thread M	M14
Bristle width L ₁	12 mm
Brush material	Stainless steel wire
Twisted knotting	left knotted
Type of product	Bevel brush