

**Cup brush Stainless steel wire 0.30 mm, Brush Ø D1: 60mm****Order data**

Order number	573205 60
GTIN	4067263906919
Item class	57H

Description**Version:**

Waved wire firmly crimped into the steel body. For use on angle grinders and on stationary machines.

With **M14 internal thread**. With **M14 internal thread**.

Application:

Very well suited for brushing surfaces, deburring, removing rust, polishing, removing paint, primer, varnish, scale etc.

Technical description

Length of brush section H ₁	20 mm
maximum speed	12000 min ⁻¹
Brush Ø D ₁	65 mm
Thread M	M14
Bristle thickness	0.3 mm
Brush material	Stainless steel wire

Twisted knotting	waved
Type of product	Cup brush