

**Cup brush Steel wire 0.35 mm, Brush Ø D1× thread M: 65XM14mm****Order data**

Order number	572050 65XM14
GTIN	4067263906933
Item class	57H

Description**Version:**

Smooth steel wire, **knotted** and firmly crimped into the steel body. **Very aggressive brushing effect with high wear resistance.**

Application:

Specially to accept angle grinders.
With **M14 internal thread.**

Technical description

maximum speed	12500 min ⁻¹
Brush Ø D ₁	65 mm
Length of brush section H ₁	20 mm
Safety support ring	no
Bristle thickness	0.35 mm
Thread M	M14
Brush material	Steel wire

Type of product

Cup brush