

**Cup brush Steel wire 0.50 mm, Brush Ø D1× thread M: 65XM14mm****Order data**

| | |
|--------------|---------------|
| Order number | 572103 65XM14 |
| GTIN | 4067263906940 |
| Item class | 57H |

Description**Version:**

Smooth steel wire, **knotted** and firmly crimped into the steel body. **Very aggressive brushing effect with high wear resistance.**

Application:

Specially to accept angle grinders.
With **M14 internal thread.**

Technical description

| | |
|--|-------------------------|
| Thread M | M14 |
| Length of brush section H ₁ | 20 mm |
| Bristle thickness | 0.5 mm |
| Safety support ring | no |
| maximum speed | 12500 min ⁻¹ |
| Brush Ø D ₁ | 65 mm |
| Brush material | Steel wire |

Type of product

Cup brush