

HOLEX**Cup brush Steel wire 0.50 mm, Brush Ø D1× thread M: 125XM14mm****Order data**

Order number	572103 125XM14
GTIN	4067263906964
Item class	57H

Description**Version:**

Smooth steel wire, **knotted** and firmly crimped into the steel body. **Very aggressive brushing effect with high wear resistance.** With **safety support ring**, after removal other bristle heights are available.

Application:

Specially to accept angle grinders.
With **M14 internal thread**.

Technical description

Length of brush section H ₁	25 + 15 mm
Thread M	M14
Safety support ring	yes
maximum speed	6500 min ⁻¹
Bristle thickness	0.5 mm
Brush Ø D ₁	125 mm

Brush material	Steel wire
Type of product	Cup brush