

**HOLEX****Cup brush Right-left knotted, steel wire 0.50 mm, Brush Ø D1× thread M: 65XM14mm****Order data**

Order number	572108 65XM14
GTIN	4067263906971
Item class	57H

**Description****Version:**

Smooth steel wire, **knotted** and firmly crimped into the steel body. **Very aggressive brushing effect with high wear resistance.**

**Right-left knotted** for increased aggressiveness for heavy-duty brushing work. Very suitable for use at corners and edges, with a smooth action.

**Application:**

Specially to accept angle grinders.

With **M14 internal thread.**

**Technical description**

Safety support ring	no
maximum speed	12500 min <sup>-1</sup>
Brush Ø D <sub>1</sub>	65 mm
Bristle thickness	0.5 mm
Length of brush section H <sub>1</sub>	20 mm

Thread M	M14
Brush material	Steel wire
Twisted knotting	Right-left knotted
Type of product	Cup brush