


**HOLEX****Wheel brush with shank Steel wire 0.30 mm, Brush  $\varnothing$  D1  $\times$  bristle width L1: 30X6mm****Order data**

Order number	574050 30X6
GTIN	4067263906988
Item class	57H

**Description****Version:**

Waved special high quality wire, **shank  $\varnothing$  6 mm.**

**Application:**

For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.

For removal of rust and scale, and for cleaning

**Technical description**

Brush $\varnothing$ D <sub>1</sub>	30 mm
Bristle thickness	0.3 mm
Bristle width L <sub>1</sub>	6 mm
Shank $\varnothing$ D <sub>s</sub>	6 mm
Length of brush section H <sub>1</sub>	6 mm
maximum speed	20000 min <sup>-1</sup>

Brush material	Steel wire
Twisted knotting	waved
Type of product	Wheel brush