


HOLEX

Wheel brush with shank Stainless steel wire 0.20 mm, Brush \varnothing D1× bristle width L1: 50X10mm



Order data

Order number	574253 50X10
GTIN	4067263934752
Item class	57H

Description

Version:

Waved special high quality wire, **shank \varnothing 6 mm.**

Application:

For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.

For removal of rust and scale, and for cleaning

Technical description

Shank \varnothing D _s	6 mm
Bristle thickness	0.2 mm
Bristle width L ₁	10 mm
maximum speed	15000 min ⁻¹
Length of brush section H ₁	12 mm
Brush \varnothing D ₁	50 mm

Brush material	Stainless steel wire
Twisted knotting	waved
Type of product	Wheel brush