

**Surface brush Steel wire 0.30 mm, Brush Ø D1: 60mm****Order data**

Order number	574755 60
GTIN	4067263935018
Item class	57H

**Description****Version:**

Area brushes with **shank Ø 6 mm.**

**Application:**

In straight die grinders, flexible shafts or on stationary machines. For cleaning and deburring small to medium-sized areas.

**Technical description**

Length of brush section H <sub>1</sub>	25 mm
Brush Ø D <sub>1</sub>	60 mm
Shank Ø D <sub>s</sub>	6 mm
Bristle thickness	0.3 mm
maximum speed	8000 min <sup>-1</sup>
Type of product	End brush

