

**Wheel brush with shank knotted, steel wire 0.50 mm, Type: 75X10****Order data**

Order number	574410 75X10
GTIN	4067263934899
Item class	57H

Description**Version:**

Knotted steel wire, **shank Ø 6 mm.**

Application:

Very aggressive brushing effect with high wear resistance. For removal of rust, scale and burrs.

Technical description

maximum speed	25000 min ⁻¹
Bristle thickness	0.5 mm
Brush Ø D ₁	75 mm
Length of brush section H ₁	15 mm
Shank Ø D _s	6 mm
Number of twisted knots	18
Bristle width L ₁	12 mm
Brush material	Steel wire

Twisted knotting	left-hand plait
Type of product	Wheel brush