

**Surface brush Steel wire 0.30 mm, Brush Ø D1: 40mm****Order data**

Order number	574755 40
GTIN	4067263935001
Item class	57H

Description**Version:**

Area brushes with **shank Ø 6 mm.**

Application:

In straight die grinders, flexible shafts or on stationary machines. For cleaning and deburring small to medium-sized areas.

Technical description

Length of brush section H ₁	20 mm
Bristle thickness	0.3 mm
maximum speed	10500 min ⁻¹
Brush Ø D ₁	40 mm
Shank Ø D _s	6 mm
Type of product	End brush

