

**Surface brush Brass wire 0.20 mm., Brush Ø D1: 50mm****Order data**

Order number	574775 50
GTIN	4067263935032
Item class	57H

Description**Version:**

Area brushes with **shank Ø 6 mm.**

Application:

In straight die grinders, flexible shafts or on stationary machines. For cleaning and deburring small to medium-sized areas.

Technical description

Bristle thickness	0.2 mm
Brush Ø D ₁	50 mm
Shank Ø D _s	6 mm
maximum speed	10500 min ⁻¹
Length of brush section H ₁	20 mm
Type of product	End brush

