

**Surface brush, plastic cup Stainless steel wire 0.30 mm, Brush Ø D1: 50mm****Order data**

Order number	574765 50
GTIN	4067263935025
Item class	57H

Description**Version:**

Area brushes with **shank Ø 6 mm**.

For **brushing stainless steel**. **Plastic cup** acts as start-up protection and prevents corrosion due to introduction of foreign materials.

Application:

In straight die grinders, flexible shafts or on stationary machines. For cleaning and deburring small to medium-sized areas.

Technical description

maximum speed	10500 min ⁻¹
Brush Ø D ₁	50 mm
Shank Ø D _s	6 mm
Bristle thickness	0.3 mm
Length of brush section H ₁	28 mm
Type of product	End brush

