

Garant**Vario plus eco blade carrier, convex for face grooving, right-hand, Ø range for groove D1 / D2: 26/34mm**

Order data

| | |
|--------------|---------------|
| Order number | 274512 26/34 |
| GTIN | 4067263934967 |
| Item class | 21U |

Description

Version:

Optimised system stability thanks to multiple screw clamping and form fit.

Suitable for:

Toolholder No. 274500 – 274503, 274530, 274531.

Attention:

Without clamping screws (these are supplied with the toolholders).

Note:

D_1 = minimum Ø for the first groove / D_2 = minimum Ø for the second groove.

Technical description

| | |
|---------------------------------|---------------------|
| maximum cutting depth t_{max} | 16 mm |
| Series | Eco |
| suitable indexable insert | No. 273656 – 273749 |
| minimum 1st groove Ø D_1 | 26 mm |

Data sheet

| | |
|--------------------------------------|------------|
| maximum 1st groove $\varnothing D_2$ | 34 mm |
| Application type | right-hand |
| Through-coolant | yes |
| Groove width w | 2 mm |
| Type of product | Cartridges |