

Garant

Vario plus eco blade carrier, convex for face grooving, right-hand, Ø range for groove D1 / D2: 82/110mm

**Order data**

Order number	274512 82/110
GTIN	4067263950325
Item class	21U

Description**Version:**

Optimised system stability thanks to multiple screw clamping and form fit.

Suitable for:

Toolholder No. 274500 – 274503, 274530, 274531.

Attention:

Without clamping screws (these are supplied with the toolholders).

Note:

D₁ = minimum Ø for the first groove / D₂ = minimum Ø for the second groove.

Technical description

minimum 1st groove Ø D ₁	82 mm
Series	Eco
maximum 1st groove Ø D ₂	110 mm
suitable indexable insert	No. 273656 – 273749

maximum cutting depth t_{\max}	16 mm
Application type	right-hand
Through-coolant	yes
Groove width w	2 mm
Type of product	Cartridges