

## Garant

**Vario plus Eco blade carrier, convex for face grooving, left-hand, Ø range for groove D1 / D2: 51/67mm**



### Order data

|              |               |
|--------------|---------------|
| Order number | 274513 51/67  |
| GTIN         | 4067263950387 |
| Item class   | 21U           |

### Description

**Version:**

Optimised system stability thanks to multiple screw clamping and form fit.

**Suitable for:**

Toolholder No. 274500 – 274503, 274530, 274531.

**Attention:**

Without clamping screws (these are supplied with the toolholders).

**Note:**

D<sub>1</sub> = minimum Ø for the first first groove / D<sub>2</sub> = minimum Ø for the second groove.

### Technical description

|  |                     |
|--|---------------------|
| suitable indexable insert              | No. 273656 – 273749 |
| maximum 1st groove Ø D <sub>2</sub>    | 67 mm               |
| maximum cutting depth t <sub>max</sub> | 16 mm               |
| Series                                 | Eco                 |

|                                      |            |
|--------------------------------------|------------|
| minimum 1st groove $\varnothing D_1$ | 51 mm      |
| Application type                     | left-hand  |
| Through-coolant                      | yes        |
| Groove width w                       | 2 mm       |
| Type of product                      | Cartridges |