

Garant

Vario plus eco blade carrier, concave for face grooving, left-hand, Ø range for groove D1 / D2: 33/43mm



Order data

| | |
|--------------|---------------|
| Order number | 274515 33/43 |
| GTIN | 4067263950523 |
| Item class | 21U |

Description

Version:

Optimised system stability thanks to multiple screw clamping and form fit.

Suitable for:

Toolholder No. 274500 – 274503, 274530, 274531.

Attention:

Without clamping screws (these are supplied with the toolholders).

Note:

D₁ = minimum Ø for the first first groove / D₂ = minimum Ø for the second groove.

Technical description

| | |
|--|---------------------|
| suitable indexable insert | No. 273656 – 273749 |
| Series | Eco |
| maximum cutting depth t _{max} | 16 mm |
| maximum 1st groove Ø D ₂ | 43 mm |

Data sheet

| | |
|--------------------------------------|------------|
| minimum 1st groove $\varnothing D_1$ | 33 mm |
| Application type | left-hand |
| Through-coolant | yes |
| Groove width w | 2 mm |
| Type of product | Cartridges |