

**Jacket Quality Dress, pale grey, Clothing size DE: 58****Order data**

| | |
|--------------|---------------|
| Order number | 091112 58 |
| GTIN | 4014382981044 |
| Item class | 09S |

Description**Version:**

Quality Dress workwear, 100 % cotton fabric. Cotton is especially resistant to chemical and mechanical influences and also to heat. Cotton is a natural product which is comfortable to wear due to its temperature-regulating properties and high absorbency.

Work jacket with mobile phone pocket.

- **Cuff with stud.**
- **Two breast pockets with flap and hook and loop fastening.**

Description:

- **Inside breast pocket.**
- **Concealed button flies.**
- **Two reinforced side pockets.**

Note:

This sizes listed in the shop are the DE clothing sizes. Please see the size table or the technical data for the corresponding sizes for your country.

Available in other colours on request.

Jacket in cornflower blue under No. 091111.

Fabric composition: 100% cotton

Material weight/fabric density: 285 g/m²

Clothing standard: UV standard 801

Washing: 60 °C coloureds

Technical description

| | |
|---|---------------------------------------|
| Position of mobile phone pocket | right-hand |
| Manufacturer's designation | Quality Dress |
| Number of side pockets | 2 |
| Side pockets | reinforced |
| Jacket closure | Button fastening |
| concealed placket | yes |
| Size FR | 54 |
| Number of breast pockets with flap and hook and loop fastening. | 2 |
| Clothing size DE | 58 |
| Collar | Non-elasticated cord in the waistband |
| Cuff | Sleeve cuff with button |
| Unisex size | XL |
| Number of inside breast pockets | 1 |
| Size UK | 42R |
| Size US | 42/34 |
| Size IT | 54 |
| Series | QUALITY DRESS |
| Special service provision | Textile finishing |
| Size ES | 54 |
| Size NL | 58 |
| Gender | Gentlemen's |
| Fabric composition | 100% cotton |
| Material weight/fabric density | 285 g/m ² |
| Clothing standard | UV standard 801 |
| Washing | 60 °C coloureds |
| Bleaching | do not bleach |

| | |
|-----------------|---|
| Dry-cleaning | Cleaning with perchlorethylene |
| Drying | gentle tumble drying (low temperature) |
| Ironing | moderately hot, up to maximum 150 °C |
| Colour | pale grey |
| Type of product | Work jacket |