

HEDI

Cable drum, sheet steel, for F, B, PL and CZ, Type: 50R



Order data

Order number	081107 50R
GTIN	4003644013494
Item class	08B

Description

Version:

Hedi® cable drums stand for “Made in Germany” quality and a long service life. The drum body is specially designed to optimally guide the cable. The integrated rotation stop switch prevents accidental drum rotation. All cable drums are equipped with thermal cut-out switches. With sockets for **the countries F, B, PL and CZ**. For use in dry environments.

Function:

IP20: Protected against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and offers no protection against water.

IP Index of Protection: IP 20

Rated power unrolled: 3500 (16 A) W

Cable class: H05RR-F

Cable structure: 3G1.5

Material cable: Rubber

Cable length: 50 m

Number of sockets: 4

Technical description

AC supply voltage	250 V
-------------------	-------

Rated power unrolled	3500 (16 A) W
Cable length	50 m
Material cable	Rubber
Cable class	H05RR-F
Cable structure	3G1.5
IP Index of Protection	IP 20
Material of body	Sheet metal
Number of sockets	4
Power supply	Mains operated
Diagnostic system present	no
Type of product	Cable drum