

## Garant

**Vario plus eco blade carrier, convex for face grooving, right-hand, Ø range for groove D1 / D2: 110/170mm**



### Order data

Order number	274520 110/170
GTIN	4067263962151
Item class	21U

### Description

**Version:**

Optimised system stability thanks to multiple screw clamping and form fit.

**Suitable for:**

Toolholder No. 274500 – 274503, 274530, 274531.

**Attention:**

Without clamping screws (these are supplied with the toolholders).

**Note:**

D<sub>1</sub> = minimum Ø for the first first groove / D<sub>2</sub> = minimum Ø for the second groove.

### Technical description

suitable indexable insert	No. 273656 – 273749
Series	Eco
minimum 1st groove Ø D <sub>1</sub>	110 mm
maximum 1st groove Ø D <sub>2</sub>	170 mm

maximum cutting depth $t_{\max}$	28 mm
Application type	right-hand
Through-coolant	yes
Groove width $w$	4 mm
Type of product	Cartridges