

Honeywell**Pair of chemical protective gloves Flextril™ 231, Glove size: 10****Order data**

Order number	094798 10
GTIN	13603835714087
Item class	04Q

Description**Version:**

Flextril™ 231. Nitrile chemical protection gloves with **medium-high cut protection**. With integrated Honeywell Moisture Dispersion Technology for high wearing comfort. High finger mobility and excellent grip thanks to the Flextril™ coating. The QR code on the back of the hand provides easy and quick access to all important technical documents and specifications. Approved for contact with foodstuffs.

Category III safety gloves.

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Glove size	10
Wall thickness	1.7 mm
Type of glove	Chemicals protection gloves
Manufacturer's designation	Flextril™ 231
Series	Flextril™

Glove characteristics	Levnedsmiddelcertificering
Protection class	Protection against bacteriological risks according to EN 374
EN 374	Type A (JKMOPT)
Resistance to chemicals	JKMOPT
EN 388	4X32C
EN 407	X1XXXX
Material	Nitrile
Backing material	Nitrile
AQL	0.65
Length	320 mm
Thickness	1.7 mm
Colour	blue/grey
Application	reusable
Cut protection class	C
Standard/regulation	EN 374
Type of product	Chemicals protection gloves