

**Honeywell****Pair of chemical protective gloves Flextril™ 231, Glove size: 11****Order data**

Order number	094798 11
GTIN	13603835714070
Item class	04Q

**Description****Version:**

**Flextril™ 231.** Nitrile chemical protection gloves with **medium-high cut protection**. With integrated Honeywell Moisture Dispersion Technology for high wearing comfort. High finger mobility and excellent grip thanks to the Flextril™ coating. The QR code on the back of the hand provides easy and quick access to all important technical documents and specifications. Approved for contact with foodstuffs.

Category III safety gloves.

**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

**Technical description**

Type of glove	Chemicals protection gloves
Manufacturer's designation	Flextril™ 231
Wall thickness	1.7 mm
Glove size	11
Series	Flextril™

Glove characteristics	Levnedsmiddelcertificering
Protection class	Protection against bacteriological risks according to EN 374
EN 374	Type A (JKMOPT)
Resistance to chemicals	JKMOPT
EN 388	4X32C
EN 407	X1XXXX
Material	Nitrile
Backing material	Nitrile
AQL	0.65
Length	320 mm
Thickness	1.7 mm
Colour	blue/grey
Application	reusable
Cut protection class	C
Standard/regulation	EN 374
Type of product	Chemicals protection gloves