

ejendals

Pair of welder's safety gloves Tegera® 19, Glove size: 11



Order data

Order number	094121 11
GTIN	7392626027473
Item class	04R

Description

Version:

Tegera® 19. All-round welder's glove made of split-grain cowhide. Very strong and tough. With elasticated band at the wrist for a better fit. Resistant to contact heat up to 100 °C. Lined.

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Manufacturer's designation	TEGERA 19
Glove size	11
Glove characteristics	Flame resistance stage 4
Application	reusable
Length	320 - 365 mm
Backing material	Split-grain cowhide
Coating variant	No coating

Contents	1
Material	Split-grain cowhide
Application range	All-round
Application range	Heavy Duty
Contact heat up to	100 °C
EN 388	3143X
EN 407	41314X
EN 12477	Type A
Welding processes	MIG/MAG
Standard	EN 407
Type of product	Welder's gloves