

ejendals

Pair of welder's safety gloves Tegera® 130A, Glove size: 9



Order data

Order number	094103 9
GTIN	7340118312507
Item class	04R

Description

Version:

Tegera® 130A. Unlined welder's glove with excellent tactile feel and reinforced index finger. The seams contain **Kevlar® thread** for use in demanding work environments. Resistant to **contact heat up to 100 °C.**

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Glove size	9
Manufacturer's designation	TEGERA 130A
Glove characteristics	Flame resistance stage 4
Application	reusable
Length	300 - 350 mm
Backing material	Full-grain goatskin
Coating variant	No coating

Contents	12
Material	Full-grain goatskin
Application range	Heavy Duty
Contact heat up to	100 °C
EN 388	3111X
EN 407	412X4X
EN 12477	Type B
Welding processes	TIG
Colour	yellow / white
Standard	EN 407
Type of product	Welder's gloves