

ejendals

Pair of gloves Tegera® 806, Glove size: 8



Order data

Order number	094572 8
GTIN	7340118396552
Item class	04R

Description

Version:

Tegera® 806. Uncoated cut-resistant glove. Ideal for use in dry areas. Thin 18-gauge knitted fabric for maximum fingertip sensitivity. Suitable for **ESD workstations**.

Standard:

EN 388; EN ISO 21420

EN 16350

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof. Gloves which protect against electrostatic discharges do not insulate the hands against electrical voltages.

Not suitable for working on live cables or for protection against electric shock - they protect only the product.

Technical description

Manufacturer's designation	TEGERA 806
Glove size	8
Contents	6

Knitted technology	18G
electrostatic characteristic	EGB/ESD
EN 388	1X42C
Backing material	Carbon, glass fibre, polyester, Spandex
Coating variant	No coating
Application range	Precision
Colour	grey
Application	reusable
Cut protection class	C
Type of product	Cut-resistant gloves