

## ejendals

### Pair of gloves Tegera® 806, Glove size: 11



#### Order data

Order number	094572 11
GTIN	7340118396828
Item class	04R

#### Description

**Version:**

**Tegera® 806.** Uncoated cut-resistant glove. Ideal for use in dry areas. Thin 18-gauge knitted fabric for maximum fingertip sensitivity. Suitable for **ESD workstations**.

**Standard:**

EN 388; EN ISO 21420

EN 16350

**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof. Gloves which protect against electrostatic discharges do not insulate the hands against electrical voltages.

Not suitable for working on live cables or for protection against electric shock - they protect only the product.

#### Technical description

Glove size	11
Manufacturer's designation	TEGERA 806
Contents	6

Knitted technology	18G
electrostatic characteristic	EGB/ESD
EN 388	1X42C
Backing material	Carbon, glass fibre, polyester, Spandex
Coating variant	No coating
Application range	Precision
Colour	grey
Application	reusable
Cut protection class	C
Type of product	Cut-resistant gloves