

**Garant****Vario plus Eco blade carrier straight, left-hand, Groove width w: 2mm**

## Order data

Order number	274511 2
GTIN	4067263120414
Item class	21U

## Description

**Suitable for:**

Vario plus Eco toolholder No. 274501; 274502; 274531.

**Attention:**

Without clamping screws (these are supplied with the toolholders).

**Note:**

With a groove width of 2 mm and 3 mm, the groove depth  $t_{\max} = 21$  mm is limited to workpiece  $\varnothing$  up to 150 mm. With a workpiece  $\varnothing > 150$  mm,  $t_{\max} = 17$  mm applies. With a groove width of 4 mm, the groove depth  $t_{\max} = 28$  mm is limited to workpiece  $\varnothing$  up to 150 mm. With a workpiece  $\varnothing > 150$  mm,  $t_{\max} = 24$  mm applies.

## Technical description

Clamping screw	279815 9
maximum cutting depth $t_{\max}$	21 mm
Series	Eco
suitable indexable insert	No. 273656 – 273749

Application type	left-hand
Through-coolant	yes
Type of product	Cartridges