

Garant
Vario plus eco toolholder straight 0°, right-hand, Shank width b: 20mm

Order data

Order number	274500 20
GTIN	4067263120445
Item class	21U

Description
Version:

Optimised system stability thanks to multiple screw clamping and form fit.

Suitable for:

Vario plus eco blade carriers No. 274512; 274514; 274516; 274518; 274520; 274522; 274540.

Supplied with:

Including assembly screws.

Note:

Coolant transfer only possible in conjunction with GARANT Master eco toolholders No. 317906 – 319136. Optional connection possibility via hose connection (G1/8 inch) No. 269207 and 269208.

Technical description

Overall length L	112.5 mm
Shank width b	20 mm
L ₁	54 mm
L ₂	43.5 mm
Clamping strip	279928 7
Clamping screw	279815 24
Assembly bolt	279815 9
Series	Eco

Application type	right-hand
Through-coolant	yes
Type of product	Toolholder