

**Garant**
**Vario plus eco toolholder straight 0°, left-hand, Shank width b: 25mm**

**Order data**

Order number	274501 25
GTIN	4067263120476
Item class	21U

**Description**
**Version:**

Optimised system stability thanks to multiple screw clamping and form fit.

**Suitable for:**

Vario plus eco blade carriers No. 274511; 274513; 274515; 274517; 274519; 274521; 274523; 274541.

**Supplied with:**

Including assembly screws.

**Note:**

Coolant transfer only possible in conjunction with GARANT Master eco toolholders No. 317906 – 319136. Optional connection possibility via hose connection (G1/8 inch) No. 269207 and 269208.

**Technical description**

Overall length L	127.5 mm
Shank width b	25 mm
L <sub>2</sub>	43.5 mm
L <sub>1</sub>	54 mm
Clamping strip	279928 7
Assembly bolt	279815 9
Clamping screw	279815 24

Series	Eco
Application type	left-hand
Through-coolant	yes
Type of product	Toolholder