

Garant
Vario plus eco toolholder straight 0°, left-hand, Shank width b: 20mm

Order data

| | |
|--------------|---------------|
| Order number | 274501 20 |
| GTIN | 4067263120469 |
| Item class | 21U |

Description
Version:

Optimised system stability thanks to multiple screw clamping and form fit.

Suitable for:

Vario plus eco blade carriers No. 274511; 274513; 274515; 274517; 274519; 274521; 274523; 274541.

Supplied with:

Including assembly screws.

Note:

Coolant transfer only possible in conjunction with GARANT Master eco toolholders No. 317906 – 319136. Optional connection possibility via hose connection (G1/8 inch) No. 269207 and 269208.

Technical description

| | |
|------------------|-----------|
| L ₂ | 43.5 mm |
| Overall length L | 112.5 mm |
| Shank width b | 20 mm |
| L ₁ | 54 mm |
| Clamping strip | 279928 7 |
| Assembly bolt | 279815 9 |
| Clamping screw | 279815 24 |

| | |
|------------------|------------|
| Series | Eco |
| Application type | left-hand |
| Through-coolant | yes |
| Type of product | Toolholder |