

Garant
Vario plus Eco toolholder cranked 90°, right-hand, Shank width b: 25mm

Order data

Order number	274502 25
GTIN	4067263120490
Item class	21U

Description
Version:

Optimised system stability thanks to multiple screw clamping and form fit.

Suitable for:

Vario plus Eco blade carriers No. 274511; 274513; 274515; 274517; 274519; 274521; 274523; 274541.

Supplied with:

Including assembly screws.

Note:

Coolant transfer only possible in conjunction with GARANT Master eco toolholders No. 317906 – 319136. Optional connection possibility via hose connection (G1/8 inch) No. 269207 and 269208.

Technical description

L ₁	54 mm
Overall length L	100 mm
Shank width b	25 mm
L ₂	16 mm
Assembly bolt	279815 9
Series	Eco

Application type	right-hand
Through-coolant	yes
Type of product	Toolholder