

**Cordless nibbler, Type: M12FNB16-0****Order data**

Order number	078105 M12FNB16-0
GTIN	4058546374112
Item class	03L

Description**Version:**

Extremely light cordless nibbler with Auto-Control start function (the cutting speed is slowly increased after start) for a working depth of up to 168 mm.

- **Tool-free cutting direction change in 90° steps.**

Supplied with:

Without battery and without charger, in a cardboard box.

Includes 2 die holders in long and short versions.

Note:

Suitable replacement batteries and chargers can be found under No. 073808 – No 073840.

Technical description

Battery voltage	12 V
Power supply	Mains operated
maximum vibration to EN	1.5 m/s ²
Cutting width	5 mm

Weight	1 kg
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	0
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
suitable battery - supplier / battery type / voltage	Milwaukee type HB 12 V
Radius of the smallest curve	40.7 mm
maximum cutting performance on steel	1.6 mm
maximum cutting performance on aluminium	2.1 mm