



Work lamp W6R-WORK



Order data

Order number	081229 W6R-WORK
GTIN	4058205030533
Item class	04B

Description

Version:

Robust, flexible, versatile: the Ledlenser W6R Work shines bright when things get tight, e.g. in cable ducts or engine compartments. In addition to the flexible attachment via stand, magnet or hook, the compact work lamp impresses with a fold-out and rotatable light head that illuminates even the narrowest gaps directly from the inside. The typical Ledlenser light beam ensures the necessary precision – either via wide-area flood light or spotlight. The powerful battery is rechargeable via USB-C. Other clever features include a nubbed surface for a strong grip, a handy transport lock and a low-battery warning function. Flexible work lamp with two light sources for floodlight or spotlight illumination. Fold-out (180°) and rotatable (270°) lamp head for illuminating hard-to-reach work areas. Robust plastic housing with non-slip surface structure. Flexible mounting via stand, magnet, and fold-out metal hook. Efficient Li-ion battery, can be easily recharged via USB-C, with battery and charge level indicator.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Technical description

Battery capacity	2.5 Ah
Bulb	LED module
ATEX zone	None

Manufacturer's designation	W6R Work
Weight	180 g
Colour temperature	6000 - 7500 K
Battery voltage	3.7 V
Illumination	220 - 600 lm
Overall length	143 mm
Power supply	Mains operated
CRI value	80
Overall width	31 mm
Illumination time	2 - 6 h
Type of rechargeable battery	Lithium-ion
IP Index of Protection	IP 54
Number of rechargeable batteries contained	1
Type of product	Work lamp