



Pen torchW2R-WORK



Order data

Order number	081227 W2R-WORK
GTIN	4058205032063
Item class	04B

Description

Version:

Precise light, always close at hand: the Ledlenser W2R Work is a rechargeable pen-shaped test light for tradespeople, construction workers and anyone in need of a reliable light in miniature format. The superior Ledlenser light quality ensures precise illumination – either via wide-area flood light or via spot LED in the light head. The W2R Work can easily be attached to breast pockets using the clip. The powerful rechargeable battery can be charged quickly and easily via USB-C. Other clever features include a nubbed surface for a strong grip, a handy transport lock and a low-battery warning function.Compact inspection light with two light sources for wide-area (flood) or spotlight (spot) illumination.Homogeneous, premium light beam for precise and even illumination.Robust plastic housing with non-slip surface structure and handy clip.Ledlenser Service-replaceable Li-ion battery; easily rechargeable via USB-C, with charge level indicator.Transport lock prevents light from being inadvertently turned on.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Technical description

Battery voltage	3.7 V
CRI value	70
Overall width	17 mm
Number of rechargeable batteries contained	1

Manufacturer's designation	W2R Work
Colour temperature	6000 - 7500 K
Battery capacity	0.63 Ah
Bulb	LED module
Overall length	176 mm
IP Index of Protection	IP 54
Type of rechargeable battery	Lithium-ion
Illumination time	1.5 - 7 h
Illumination	60 - 220 lm
Power supply	Mains operated
Weight	61 g
ATEX zone	None
Type of product	Work lamp