



Work lamp W7R-WORK



Order data

Order number	081229 W7R-WORK
GTIN	4058205030564
Item class	04B

Description

Version:

Clever, innovative, versatile: the Ledlenser W7R Work is the ultimate work light for professionals with continuously adjustable colour temperature depending on the application scenario and additional UV light in the lamp head for leak detection or document inspection. The fold-out and rotatable lamp head illuminates even narrow working areas. The typical Ledlenser light beam ensures the necessary precision and is continuously adjustable between warm white and cool white light. The powerful battery of the W7R Work can be recharged via USB-C. Other useful features include numerous mounting options and the handy transport lock.

- **Flexible premium work light with two light sources for wide-area illumination and UV light (365 nm) for leak detection or checking documents.**
- **Continuously adjustable colour temperature for different use cases.**
- **Fold-out (180°) and rotatable (270°) lamp head for illuminating hard-to-reach work areas.**
- **Flexible mounting via stand, magnet, and fold-out metal hook.**
- **Efficient Li-ion battery, rechargeable via USB-C.**

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Technical description

Illumination time	2 - 5 h
Manufacturer's designation	W7R Work

Number of rechargeable batteries contained	1
CRI value	80
Bulb	LED module
Weight	180 g
Overall width	31 mm
Battery voltage	3.7 V
Type of rechargeable battery	Lithium-ion
Power supply	Mains operated
Battery capacity	2.5 Ah
Illumination	220 - 600 lm
IP Index of Protection	IP 54
Colour temperature	4000 - 7500 K
ATEX zone	None
Overall length	143 mm
Type of product	Work lamp