



Work lamp W5R-WORK



Order data

Order number	081228 W5R-WORK
GTIN	4058205030502
Item class	04B

Description

Version:

Robust, reliable, powerful: the Ledlenser W5R Work is the luminous powerhouse in trade professionals' toolboxes. The typical Ledlenser premium light beam ensures precise illumination even of larger work areas – either via floodlight or spotlight. Thanks to the integrated magnet and hook in the stand, the W5R Work can be flexibly positioned and aligned at any time. The powerful battery can be recharged quickly and easily via USB-C. Other clever features include a metal screw for tightening the foldable stand, a nubbed surface for a strong grip and a handy transport lock. Powerful work light with two light sources for flood or spot illumination. Robust plastic housing with non-slip surface structure. Flexible mounting and illumination thanks to hook, magnet and folding mechanism. Efficient Li-ion battery, can be easily recharged via USB-C, with battery and charge level indicator. Transport lock prevents light from being inadvertently turned on.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Technical description

CRI value	80
Weight	153 g
Number of rechargeable batteries contained	1

Illumination time	3 - 6 h
Battery voltage	3.7 V
Manufacturer's designation	W5R Work
Illumination	220 - 600 lm
Colour temperature	6000 - 7500 K
IP Index of Protection	IP 54
Type of rechargeable battery	Lithium-ion
Overall length	153 mm
Bulb	LED module
ATEX zone	None
Overall width	38 mm
Battery capacity	2.5 Ah
Power supply	Mains operated
Type of product	Work lamp