



Pen torchW2-WORK



Order data

Order number	081227 W2-WORK
GTIN	4058205032032
Item class	04B

Description

Version:

Precise light, always close at hand: the Ledlenser W2 Work is a battery-powered pen and test light for tradespeople, construction workers and anyone in need of a reliable light in miniature format. The superior Ledlenser light quality ensures precise illumination – either via wide-area flood light or via spot LED in the light head. The W2 Work can easily be attached to breast pockets using the clip. Other clever features include a nubbed surface for a strong grip, a handy transport lock and a low-battery warning function. Two AAA batteries make for a reliable and easy energy supply for its next use. Compact format, fits in a trousers pocket. Three lighting options, including a focussable spotlight with a reflector lens in the lamp head. Battery status indicator. Integral magnet for easy attachment to metal surfaces (such as to steel girders or motors). Tipping mechanism permits flexible alignment for optimum illumination of the working area.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Technical description

ATEX zone	None
Colour temperature	6000 - 7500 K
Overall height	176 mm
Weight	42 g

Manufacturer's designation	W2 Work
Battery type	Micro, AAA
Overall length	24 mm
Power supply	Battery-powered
IP Index of Protection	IP 54
Illumination	40 - 160 lm
Number of batteries contained	2
Bulb	LED module
Overall width	17 mm
CRI value	70
Illumination time	10 h
Type of product	Work lamp