



Work lamp W4R-WORK



Order data

Order number	081228 W4R-WORK
GTIN	4058205030441
Item class	04B

Description

Version:

Robust, versatile, compact: the Ledlenser W4R Work is a reliable work light for everyday workshop use. The typical Ledlenser premium light beam ensures precise and powerful illumination of work areas – either via floodlight or spotlight. Thanks to the integrated magnet and swivelling base, the W4R Work can be flexibly positioned and aligned at any time. The powerful battery can be recharged quickly and easily via USB-C. Other clever features include a clip for attaching to work clothing or equipment, a nubbed surface for a strong grip and a handy transport lock. Compact work light with two light sources for wide-area (flood) or spotlight (spot) illumination. Robust plastic housing with non-slip surface structure. Flexible mounting and illumination thanks to the magnet and swivel mechanism. Efficient Li-ion battery, can be easily recharged via USB-C, with battery and charge level indicator. Transport lock prevents light from being inadvertently turned on.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Technical description

Illumination time	2 - 9 h
Overall width	28 mm
Weight	91 g
Illumination	60 - 220 lm

CRI value	70
Number of rechargeable batteries contained	1
ATEX zone	None
Manufacturer's designation	W4R Work
Bulb	LED module
Type of rechargeable battery	Lithium-ion
Battery capacity	0.76 Ah
Overall length	163 mm
Power supply	Mains operated
IP Index of Protection	IP 54
Battery voltage	3.7 V
Colour temperature	6000 - 7500 K
Type of product	Work lamp